


# High Tech Soft PU Foaming Technology

---

Using high-quality environmental protection PU material and high-tech foaming technology, it is formed in one, free of harmful substances, healthy and tasteless. The material has good physical properties, no deformation after long pressure and full durability



# PRODUCT DETAILS



positive

The front leather grain design can effectively prevent slip. You don't have to worry about falling when standing on it



back

The bottom grain is wear-resistant and anti sliding layer, waterproof and anti fouling, which can effectively protect the floor and is not easy to curl

# A Variety Of Barber Chairs Are Applicable

You can customize your chair according to the shape of the hair chair



Long bottom



Round bottom



Hollow bottom



# DESIGN OF DECOMPRESSION AND ANTI FATIGUE FLOOR MAT

---

Scientific and practical design can reduce the influence of gravity, analyze the pressure on the human body, and reduce the damage to the waist, ankle and knee joint caused by standing for a long time. Barbers will prepare such decompression mats for barbers



## PRODUCT INFORMATION

---

**Brand:** Finehope

**Colour:** Customizable

**Apply:** Currency

**Place Of Origin:** Xiamen, Fujian

**Texture Of Material:** Polyurethane



## Comfortable Decompression · Standing Pad


Long standing without fatigue  
Decompression and anti fatigue



# USAGE SCENARIO

## usage scenario of anti fatigue floor mat

Anti fatigue mat for a long time can effectively alleviate the fatigue of barbers standing for a long time. The mat has strong compression resistance and genuine quality assurance. It is the favorite of barbers.



**Finehope ha ottenuto il certificato ISO 9001 ininterrottamente dal 2003.**

### **Certificazione IATF16949:**

#### **[Fornitore di materiali da costruzione in schiuma rigida in PU in Cina](#)**

Finehope ha superato la certificazione IATF16949 dei sistemi di gestione della qualità automobilistica nel 2021. Oltre 50 documenti garantiscono il progresso dello sviluppo di nuovi prodotti, la qualità, i tempi di consegna e i costi dei prodotti di prova e di produzione di massa.

Dalla collaborazione tra Finehope e Caterpillar nel 2007, Finehope ha utilizzato il sistema di gestione della qualità automobilistica per l'introduzione di nuovi prodotti, utilizzando i cinque strumenti SPC, MSA, FMEA, APQP e PPAP, che hanno ottenuto elogi dai dirigenti Caterpillar e stabilito un lungo partnership a lungo termine finora.

»»» Our Advandages





### Capacità di ricerca e sviluppo di materie prime PU

Dal 2002, Finehope è impegnata nella progettazione e produzione di prodotti in schiuma stampata in PU. La ricerca e lo sviluppo indipendenti di materiali formulati e una capacità produttiva stabile sono la base per la garanzia della qualità.


Finehope può adattare la formula del prodotto in qualsiasi momento in base alle esigenze personalizzate dei prodotti personalizzati dei clienti, come i requisiti di durezza, elasticità, supporto, sensazione, densità, colore e altre proprietà fisiche e chimiche, e può soddisfare i requisiti di formulazione con le leggi e i regolamenti dei vari paesi.

Naturalmente, una buona formula deve anche considerare la migliore prestazione in termini di costi. Per i nuovi progetti, la capacità di sviluppare formulazioni PU è una condizione chiave per garantire la qualità dello sviluppo del prodotto, i tempi di consegna e i costi.

### Capacità di progettazione e produzione di apparecchiature di automazione

La capacità di Finehope di progettare e produrre apparecchiature di automazione è rara nel settore. Partecipando alla progettazione di nuove apparecchiature di miscelazione per iniezione di PU e alla trasformazione automatizzata della linea di produzione, per garantire che, sotto la concorrenza del dividendo demografico cinese, venga ridotto e i costi della manodopera continuano ad aumentare, è possibile migliorare anche l'efficienza produttiva e ridurre i costi della manodopera e dei materiali. Inoltre, le continue capacità di progettazione e produzione di attrezzature chiave come dispositivi, attrezzature speciali e stampi automatici sono anche le ragioni per cui Finehope è in una posizione di leadership sotto tutti gli aspetti.

La capacità di Finehope di ridurre continuamente i costi e innovare i prodotti può aiutare i clienti ad apportare maggiore valore. Pertanto, è un partner affidabile a lungo termine di molte aziende Fortune 500 e aziende leader del settore.



### Capacità di gestione scientifica

Finehope sottolinea l'importanza del Toyota Production System e del modello di Corporate Coaching per ottimizzare l'efficienza gestionale. Miglioramento continuo, l'efficienza e la qualità di tutti i dipendenti, del personale dirigente e di produzione sono state migliorate in modo efficace e continuo, i costi di gestione e di produzione sono stati continuamente ridotti, ma più importante di efficienza e costi sono la coltivazione della crescita dei dipendenti attraverso il miglioramento continuo, perché questo è il nucleo dello sviluppo sostenibile aziendale.

[Fabbrica cinese di schiuma di poliuretano pu](#) La raffinatezza di Finehope riduce i problemi per i clienti, perché riduce la negligenza nel sistema dei processi umani e la capacità di accumulare continuamente esperienza professionale, che può garantire che tutti i nuovi progetti siano completati nel più breve tempo possibile.

# Famous customer

Cooperation experience

Engineering  
Vehicle

BOYD  
CORPORATION

TVH

AIXAM

Honeywell | STIGA | CAT

Medical  
Equipment

Hill-Rom

INVACARE  
Yes, you can.

MAQUET  
GETINGE GROUP

Dr Posture

Ki Mobility

Baby  
Supplies

Bumbo Nuby

bugaboo

chicco

Hatch  
Baby

GRACO

Fitness  
Equipment

STAR TRAC  
expect different.

BOWFLEX

IB&G  
BUILDING PRODUCTS

ergoDRIVEN

NUVA

Other

PANDORA  
UNFORGETTABLE MOMENTS

Cubefit

Knoll

## FAQ

### 1. Perché scegli Finehope?

Finehope è il produttore di PU più professionale in Cina, che dispone di un team di ricerca e sviluppo professionale, apparecchiature avanzate per la produzione di PU, apparecchiature di prova professionali e un perfetto sistema di gestione della qualità. Abbiamo 12 anni di esperienza di cooperazione con CAT, FIAT, TVH, STIGA e altre aziende famose. Forniamo loro un servizio in una sola fase, dalla ricerca e sviluppo alla produzione, per soddisfare le loro esigenze di personalizzazione.

### 2. Quali sono i vantaggi di scegliere Finehope?

- 1) Garanzia della qualità del prodotto, garanzia di consegna, buon servizio post-vendita.
- 2) Efficienza di sviluppo economica e rapida, funzionamento professionale con integrità.
- 3) Finehope condurrà tutte le analisi dei test e quindi elaborerà gli standard di test per ridurre le controversie sugli standard di qualità clienti e produttori.
- 4) Modalità di gestione della produzione snella.
- 5) Aiutare i clienti a sviluppare e progettare nuovi prodotti.
- 6) Ha una ricca esperienza nella progettazione e lavorazione di prodotti in PU.
- 7) Finehope è un'impresa high-tech in Cina con brevetti di invenzione nazionali e internazionali tecnologici e intellettuali proprietà.

### 3. Quali sono le differenze tra Finehope e i coetanei nazionali?

- 1) Assicurazione della qualità: pianificazione avanzata della qualità (APQP).
- 2) Finehope ha una ricca esperienza nel servire grandi imprese internazionali.
- 3) Dispone di un gruppo di ricerca scientifica professionale di materiale poliuretano.



- 4) Ha capacità di progettazione, produzione e innovazione indipendenti di attrezzature e stampi di produzione.
- 5) Dispone di un team di ingegneri responsabile del sistema di garanzia della qualità e del controllo di qualità.

#### **4. Quali sono le differenze tra Finehope e i suoi colleghi europei e statunitensi?**

- 1) Ha una catena di fornitura di supporto perfetta e matura.
- 2) Riduzione dei costi degli stampi.
- 3) Alta efficienza di sviluppo e capacità di progettazione e tempi di processo brevi.
- 4) Vantaggio in termini di costi e buona attitudine al servizio.

#### **5. Quali sono le applicazioni dei prodotti PU?**

Auto, macchinari per l'ingegneria, attrezzature per il fitness sportivo, macchinari medici e articoli per la casa di uso quotidiano e così via.



## About us



OUR  
BUILDING









## Our Certification



**Xiamen Micro, Piccole e Medie  
Imprese orientate alla crescita**



**Xiamen PMI specializzate, raffinate,  
differenziate e innovative**



**Xiamen Scienza e Tecnologia Piccola  
gigantesca impresa leader**



Finehope è stata classificata come "Micro, piccole e medie imprese orientate alla crescita di Xiamen" dal 2019.

Si tratta del risultato del punteggio del governo municipale di Xiamen basato sui vari indicatori completi, sui modelli di crescita, sulla forza del marchio nel settore e sulla buona reputazione aziendale di Finehope, quindi rilascia questo certificato. È una prova che Finehope si distingue tra migliaia di piccole e medie imprese della città.

Finehope è stata classificata come "PMI Xiamen specializzate, raffinate, differenziate, innovative" dal 2020. "Specializzata, raffinazione, differenziata, innovativa" si riferisce alle PMI con attività principali eccezionali, forti capacità professionali, forti capacità di ricerca e sviluppo e innovazione e potenziale di sviluppo. Principalmente concentrato nella nuova generazione di tecnologia dell'informazione, produzione di apparecchiature di fascia alta, nuova energia, nuovi materiali, biomedicina e altre industrie di fascia medio-alta. Il governo sottolinea e riconosce la "specializzazione, l'innovazione speciale" di Finehope è quella di incoraggiare l'innovazione e raggiungere la specializzazione, la riforma e la specializzazione.

Dal 2019, Finehope è stata selezionata come azienda leader di Xiamen Science and Technology Little Giant. Questo certificato è stato rilasciato congiuntamente da cinque dipartimenti del governo municipale di Xiamen. I criteri di selezione si concentrano su settori strategici emergenti come la tecnologia dell'informazione di nuova generazione, apparecchiature di fascia alta, nuovi materiali, nuova energia, biologia e nuova medicina, risparmio energetico e protezione ambientale e alta tecnologia marina. Vincere questo onore dimostra che Finehope è in prima linea nel settore delle nuove tecnologie dell'informazione e dei nuovi materiali.



### Certificazione della Food and Drug Administration

Da allora Finehope ha superato la certificazione della Food and Drug Administration ogni anno 2018. L'approvazione della Food and Drug Administration significa che i prodotti fabbricati da Finehope hanno ottenuto certificati governativi stranieri (CFG) e possono entrare senza problemi nel mercato globale.



### Certificato di integrazione del sistema di gestione dell'informazione e dell'industrializzazione

Il certificato viene valutato dal governo municipale di Xiamen e rilasciato dall'Accademia di scienze della gestione della qualità di Shanghai. Questo certificato riflette il livello di profonda integrazione di informatizzazione e industrializzazione di Finehope. Finehope continuerà a intraprendere una nuova strada



### Certificato di standardizzazione della sicurezza sul lavoro

La sicurezza della produzione è importante per prevenire o ridurre il rischio di infortuni sul lavoro, malattie e morte. Tiger Side, direttore generale di Finehope: "Solo gli impianti di produzione che continuano a porre l'accento sulla sicurezza come questione di primo livello rimarranno altamente produttivi e competitivi nel mercato odierno."





# Quality Assurance



UNIVERSAL TESTING MACHINE(UTM)



Tensile Test



Tear Resistance Test



Compressive Strength



Indentation Force Deflection



## INSPECTION STANDARD

## MATERIAL PERFORMANCE TEST REPORT

**Finehope**  
**Test Report** No. 00201457201 Date: 20140723 Page 1/4  
 Customer: CUSTOMER SERVICE DEPARTMENT

The following samples were submitted and identified by/on behalf of the client as:

Sample Description: UHMW and MHD (underdevelopment)  
 Material No.: 1  
 Other info.: 1  
 Sample Processing Date: 20140724  
 Working Process: 20140723

**Test Method**

- 001 ASTM D2014-2011 Test of Density, Test Agency
- 002 ASTM D2014-2011 Test of Density, Test Agency
- 003 ASTM D2014-2011 Test of Density, Test Agency
- 004 ASTM D2014-2011 Test of Density, Test Agency
- 005 ASTM D2014-2011 Test of Density, Test Agency
- 006 ASTM D2014-2011 Test of Density, Test Agency
- 007 ASTM D2014-2011 Test of Density, Test Agency
- 008 ASTM D2014-2011 Test of Density, Test Agency
- 009 ASTM D2014-2011 Test of Density, Test Agency
- 010 ASTM D2014-2011 Test of Density, Test Agency
- 011 ASTM D2014-2011 Test of Density, Test Agency
- 012 ASTM D2014-2011 Test of Density, Test Agency
- 013 ASTM D2014-2011 Test of Density, Test Agency
- 014 ASTM D2014-2011 Test of Density, Test Agency
- 015 ASTM D2014-2011 Test of Density, Test Agency
- 016 ASTM D2014-2011 Test of Density, Test Agency
- 017 ASTM D2014-2011 Test of Density, Test Agency
- 018 ASTM D2014-2011 Test of Density, Test Agency
- 019 ASTM D2014-2011 Test of Density, Test Agency
- 020 ASTM D2014-2011 Test of Density, Test Agency

**Finehope**  
**Test Report** No. 00201457201 Date: 20140723 Page 2/4  
 Customer: CUSTOMER SERVICE DEPARTMENT

**Test Result**

No.	Test Item	Test Standard	Customer Requirement	Customer Sample group			Customer Sample Unit		
				1	2	3	1	2	3
1	Density	ASTM D2014-2011	0.93	0.93	0.93	0.93	0.93	0.93	
2	Hardness	ASTM D2014-2011	60	60	60	60	60	60	
3	Strength	ASTM D2014-2011	10	10	10	10	10	10	
4	Impact	ASTM D2014-2011	10	10	10	10	10	10	
5	Modulus	ASTM D2014-2011	10	10	10	10	10	10	
6	Creep	ASTM D2014-2011	10	10	10	10	10	10	
7	Relaxation	ASTM D2014-2011	10	10	10	10	10	10	

FIG. 1. In order to make the strength of two steel rods can be compared, see the test specimen in the same background color. The red rod is the test specimen in the same background color. The blue rod is the test specimen in the same background color.

FIG. 2. For the specific grade value in the above test result, it is the value of specimen with the same color and the actual value of the whole sample.

**Finehope**  
**Test Report** No. 00201457201 Date: 20140723 Page 3/4  
 Customer: CUSTOMER SERVICE DEPARTMENT

**Sketch Picture**

1. This picture is only used with the Serial Report from Finehope.

<b>Customer</b>	
<b>Location</b>	New Zealand
<b>Customer Code</b>	G1019
<b>Risk Assessment</b>	
<b>New:</b>	Site <input type="checkbox"/> Technology <input type="checkbox"/> Process <input type="checkbox"/>
<b>Other Risks</b>	<input type="checkbox"/>

<b>Project</b>	
<b>Finehope Contact</b>	Wendy Yang
<b>Part No.</b>	
<b>Part Name</b>	G1019Y04
<b>Change Level/Date</b>	
<b>User Plant(s)</b>	Finehope

Core Team Members	Company/Title	Phone/Fax/E-Mail
Tiger Xu	G.M.	
Yibin Lim	Vice G.M.	
Cindy Wu	Sales Manager	<a href="mailto:cindy@finehope.com">cindy@finehope.com</a>
Liangquan Wan	Project Manager	
Wendy Yang	Sales	<a href="mailto:wendy@finehope.com">wendy@finehope.com</a>

Build Level	Material Required Date	Quantity	No. Concurrent	
			SRCs	Majors
Product Design and Develop	21-Jun-21	10		
Product and Process Validat	25-Jun-21	15		

APQP Deliverable	Finehope APQP Reference Only	G Y R	Project Need Date	Supplier Timing Date	Actual Closure Date	Supplier Lead Resp Inits	Finehope Acceptance Complete	Remarks or Assistance Required
1. Project Timeline (Synchronized w/Production Time Plan)	2030	G	20-Jun-21	21-Jun-21	21-Jun-21	22-Jun-21	23-Jun-21	/
2. Customer Inputs / Requirements	2030	G	23-Jun-21	24-Jun-21	24-Jun-21	25-Jun-21	26-Jun-21	/
3. Warranty & Quality Mitigation Plan	2030	G	24-Jun-21	25-Jun-21	25-Jun-21	26-Jun-21	27-Jun-21	/
4. Customer Specific Requirements	2030	G	25-Jun-21	26-Jun-21	26-Jun-21	27-Jun-21	28-Jun-21	/
5. Design FMEA	2080	G	26-Jun-21	27-Jun-21	27-Jun-21	28-Jun-21	29-Jun-21	/
6. Preliminary Bill of Materials (BOM)	2030	G	27-Jun-21	28-Jun-21	28-Jun-21	29-Jun-21	30-Jun-21	/
7. Prototype Control Plans	2110	G	28-Jun-21	29-Jun-21	29-Jun-21	30-Jun-21	1-Jul-21	/
8. Prototype Builds	2110	G	29-Jun-21	30-Jun-21	30-Jun-21	1-Jul-21	2-Jul-21	/
9. Design Verification Plan & Report (DVP&R)	2120	G	30-Jun-21	1-Jul-21	1-Jul-21	2-Jul-21	3-Jul-21	/
10. Design / Process Review	2130	G	1-Jul-21	2-Jul-21	2-Jul-21	3-Jul-21	4-Jul-21	/
11. Team Feasibility Commitment	2130	G	2-Jul-21	3-Jul-21	3-Jul-21	4-Jul-21	5-Jul-21	/
12. APQP Status Sub-Supplier	2130	G	3-Jul-21	4-Jul-21	4-Jul-21	5-Jul-21	6-Jul-21	/
13. Production Drawing & Specifications	2220	G	4-Jul-21	5-Jul-21	5-Jul-21	6-Jul-21	7-Jul-21	/
14. Subcontractor Purchase Orders (Customer Tooling)	2220	G	5-Jul-21	6-Jul-21	6-Jul-21	7-Jul-21	8-Jul-21	/
15. Facilities, Equipment, Tools and Gages	2260	G	6-Jul-21	7-Jul-21	7-Jul-21	8-Jul-21	9-Jul-21	/
AIAG APQP Phase 3 - Process Design and Development								
16. Product/Process and Quality System Review	3030	G	9-Jul-21	10-Jul-21	10-Jul-21	10-Jul-21	11-Jul-21	/
17. Manufacturing Process Flow Chart	3040	G	11-Jul-21	12-Jul-21	12-Jul-21	12-Jul-21	13-Jul-21	/
18. Process FMEA	3100	G	13-Jul-21	14-Jul-21	14-Jul-21	14-Jul-21	15-Jul-21	/
19. Pre-Launch Control Plan	3110	G	15-Jul-21	16-Jul-21	16-Jul-21	16-Jul-21	17-Jul-21	/
20. Process Work Instructions	3120	G	17-Jul-21	18-Jul-21	18-Jul-21	18-Jul-21	19-Jul-21	/
21. Measurement Systems Evaluation	3130	G	19-Jul-21	20-Jul-21	20-Jul-21	20-Jul-21	21-Jul-21	/
22. Packaging Specifications & Approvals	3160	G	21-Jul-21	22-Jul-21	22-Jul-21	22-Jul-21	23-Jul-21	/
23. Manufacturing Team Training	3170	G	23-Jul-21	24-Jul-21	24-Jul-21	24-Jul-21	25-Jul-21	/
AIAG APQP Phase 4 - Product and Process Validation								
24. Subcontractor PPAP Approval	4005	G	9-Jul-21	10-Jul-21	10-Jul-21	10-Jul-21	11-Jul-21	/
25. Production Control Plan	4008	G	11-Jul-21	12-Jul-21	12-Jul-21	12-Jul-21	13-Jul-21	/
26. Production Readiness Review (PRR)	4009	G	13-Jul-21	14-Jul-21	14-Jul-21	14-Jul-21	15-Jul-21	/
27. Production Trial Run (PTR)	4010	G	15-Jul-21	16-Jul-21	16-Jul-21	16-Jul-21	17-Jul-21	/
28. Process Capability Studies	4030	G	17-Jul-21	18-Jul-21	18-Jul-21	18-Jul-21	19-Jul-21	/
29. Production Validation Plan & Report (PV&R)	4090	G	19-Jul-21	20-Jul-21	20-Jul-21	20-Jul-21	21-Jul-21	/
30. Production Part Approval (PPAP)	4110	G	21-Jul-21	22-Jul-21	22-Jul-21	22-Jul-21	23-Jul-21	/
AIAG APQP Phase 5 - Feedback, Assessment and Corrective Action								
31. Initial Production Shipment	5005	G	20-Jul-21	30-Jul-21	30-Jul-21	30-Jul-21	31-Jul-21	/
32. Production Ramp-up Plan	5005	G	31-Jul-21	2-Aug-21	2-Aug-21	2-Aug-21	3-Aug-21	/
33. Full Production Date	5005	G	5-Aug-21	7-Aug-21	7-Aug-21	7-Aug-21	8-Aug-21	/
34. Conduct Lessons Learned	5005	G	8-Aug-21	10-Aug-21	10-Aug-21	10-Aug-21	11-Aug-21	/



## Design Failure Mode and Effects Analysis (Design FMEA)

FMEA No.:  
DFMEA-001

Page: page 1, totally 3 pages  
Made: Xiaodong Qiu

Product Name: Injection moulding

Procedure responsible dept: Production Dept

Model year/vehicle types: CRV

Soybean Milk Maker

Important date: Nov.10th.2015

FMEA Date: Nov.10th.2015

People participated: Develop dept:GaoLin Wei

Sales:Haiyan Wu

PC:Jiannan Yan

Technology Dept:Jianyu Zhou

Purchaser:Yuanyuan Gou

Production dept:Shuwen Dong

QC:Bingxiang Zheng

procedure function requirements	Potential failure mode	Potential effects analysis	severity (S)	grade	potential causes/mechanisms of failure	frequency (O)	Current prevention process control	Current detection process control	detection (D)	RPN	recommended measures	Responsibility and target completion date	action results				
													severity (S)	frequency (O)	difficult to check (D)	RPN	
scyphus	size changes of handle	handle cover fall off	6	A	PP size change	6	By adjusting the product of the injection molding process, and measure or test the clasp of product size	measure and test product size	3	108	Add the number of button bit in handle design, in order to keep the connection strength	Xiaodong Qiu 2015/08/25	By adjusting the product of the injection molding process, and measure or test product size	6	1	1	6
scyphus	warping of scyphus handle	Poor appearance break	4	C	high handle wall	6	Add the stiffener to handle wall to prevent deformation	measure and test product size	2	48	if this problem appears, make improvement by Adding the stiffener	Xiaodong Qiu 2015/09/30	Add the stiffener to handle wall to prevent deformation	4	2	1	8
scyphus	Deformation of cup-mouth	Micro switch without power	8	A	PP material deformation, Resulting in a perpendicular direction to connect the cup and handle inward deformation, So that both sides of the 球, the micro switch column opposite sink., and	3	Adjust the injection molding process, to prevent extrusion	measure and test cup-mouth size	3	72	in the cup packing control the direction of the lateral dimension of no force, stipulate the way of packing	Xiaodong Qiu 2015/09/10	stipulate the cup use egg cell methods to put the packing which do not squeeze each other	8	1	3	24

H-R-P-001-1

## Process Failure Mode and Effects Analysis (PFMEA)

潜在失效模式和后果分析

FMEA No.FMEA20150325-01

Page 3

Maint:Wenhong-Huang

FMEA Date (Original):2015.03.25

Item:Welding Improvement

Process Responsibilities: Production welding group

Model year/project

Key Dates

Item 项目	Potential failure mode 潜在失效模式	Potential consequences of failure modes 失效的后果/潜在失效模式	Severity 严重度	Grade 等级	Potential causes of failure 失效的潜在原因	Occurrence degree 发生度	Current process control and prevention 现行过程控制/预防	Current process control detection 现行过程控制/检测	Detection rate 检测率	RPN	Suggest measures 建议措施	Responsibility and target completion date 责任及目标完成日期	Measure results/测量结果			
													Measures and effective date 措施及有效日期	Severity 严重度	Incidence rate 发生率	Detection degree 可检测度
Clamping is not in place 夹具不在位	SizeNG 尺寸NG		6	B	● Staff negligence 人员疏忽 ● Failure for bad 夹具不到位	4	● Make the operation standard book 制定作业标准书 ● Make maintenance standards, regular maintenance 制定保养标准,定期保养,维护	● Visual inspection 目视检测 ● Finished 100% full inspection 完成100%全检	6	144	● Pre-service training of staff 岗前培训 ● Regular maintenance 工器具定期维护		6	3	4	72
Clamping (clamping required is in place, no missing or wrong loaded) 夹具不在位,无漏装/错装	Welding error, leak, welding deviation, affect the assembly or use function 焊接错误,漏焊,焊接偏差,影响装配或使用功能		8	A	● Staff negligence 人员疏忽 ● Failure for bad 夹具不到位 ● Failure inaccurate 夹具定位不准确	4	● Make the operation standard book 制定作业标准书 ● Make maintenance standards, regular maintenance 制定保养标准,定期保养,维护 ● Regular checking of fixture 夹具定期点检	Visual inspection 目视检测	6	192	● Pre-service training of staff 岗前培训 ● Regular maintenance 工器具定期维护 ● Make inspection checklist for fixture 夹具点检表		8	3	4	96
Attachments missing 附件缺失	Affect product strength or influence the assembly 影响产品强度或影响装配		8	A	Staff negligence 作业人员疏忽	3	Make the operation standard book 制定作业标准书	Visual inspection 目视检测	4	96	Final inspection personnel do 100% full inspection for each bead with man 每粒人工100%全检,确认		8	2	2	32
Attachment error 附件错误	Influence assembly 影响装配		7	A	No mistake proofing fixture 无防错夹具	3	Make the operation standard book 制定作业标准书	Visual inspection 目视检测	6	126	● Increase the mistake proofing devices 增加防错装置 ● Inspection for final inspection tools 夹具定期点检		7	2	4	56
False welding 假焊	Lack of strength, affect the use of function 强度不足,影响使用功能		9	A	Current, voltage, welding angle, speed setting is not reasonable 电流,电压,焊接角度,速度设置不合理	4	● Welding process guidance 制定焊接工艺指导书 ● Condition confirmation check 加工条件确认书 ● Confirm the failure test on a regular basis 定期开展失效测试	Destructive testing 破坏性试验	8	288	After the procedure is set up to confirm the processing conditions, the execution and marking of the failure test is performed. 工序设置完成后确认加工条件		9	3	4	108

# Production Device

## KRAUSS MAFFEI

Finehope has successively introduced many of the world's most advanced German KraussMaffei high-pressure injection machines since 2010.



Reaction Injection Molding (RIM) High Pressure Machine KRAUSS MAFFEI Made in Germany!



## Self-invented fully automatic production line

Finehope has independently developed a number of fully automatic P-U injection production lines since 2010. These production lines reduce production costs and meet customer delivery requirements.



## Welding Robots



Since 2016, Finehope has continued to purchase welding robots and automatic fixture turntables for welding metal parts. The independent processing of accessories saves the waiting time and procurement cost of outsourcing processing.

## CNC Machine

Finehope has continued to purchase CNC equipment since 2016. CNC (Computer Numerically Controlled) machining is a manufacturing process in which pre-programmed computer software dictates the movement of factory tools and machinery. Using this type of machine versus manual machining can result in improved accuracy, increased production speeds, enhanced safety, increased efficiency and most importantly, help customers save costs and improve product quality.



## Mould Release Agent Painting Robot



Since 2019, Finehope has purchased robots for spraying water-based release agents to improve the working environment, improve spraying quality and material utilization, and reduce labor costs.

## 3D printer

Finehope started to purchase 3D printers in 2015. 3D printing can realize rapid proofing of new product prototypes and templates for resin molds, and can also be used for faster and cheaper small batch production.



# Social Responsibility

- **Audited by Sedex**

(Supplier business ethics information exchange )

Labor standard · health and safety · Environmental protection · Business ethics practice

- **Public-spirited**



Voluntary tree planting after Super Typhoon Meranti in 2016

## A VALUE-BASED COMPANY



CUSTOMER FIRST

TEAMWORK

EMBRACE CHANGES

PASSION

INTEGRITY

COMMITMENT

